

SKINTOP® ST-M L-BOXX

Being organised is essential. With our product case for SKINTOP® ST-M cable glands with a component insert and transparent lid, you always have the right thread size at hand. Thanks to its robust design, integration in vehicle equipment systems and the snap-in system for combination with other cases, it is perfectly suited for assembly use.



Преимущества

Inset for loose components ensures optimum organisation and prevents mixing of the items.

Case made of light and robust, shock- and impact-resistant ABS plastic.

Intelligent snap system allows quick connection, combination and disconnection of cases, saving time and energy during transport.

Easy integration in vehicle equipment systems of numerous manufacturers.

Transparent lid allows a perfect overview even when closed.

Области применения

For safe transport and storage of SKINTOP® ST-M cable glands (sizes M12 to M32).

Especially for assembly use, e.g. on the construction site.

Характеристики

Two robust locking mechanisms ensure a secure closure.

Case can be refilled with standard packaging units.

Mounting instruction and locknut included.

Комплектация

SKINTOP® ST-M M12 / 50 pieces

SKINTOP® ST-M M16 / 50 pieces

SKINTOP® ST-M M20 / 25 pieces

SKINTOP® ST-M M25 / 25 pieces

SKINTOP® ST-M M32 / 5 pieces

Counter nut SKINTOP® GMP-GL-M included

Техническая информация

Классификация ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: кабельный ввод с резьбой

Классификация ETIM 6:

Обозначение класса ETIM 6.0: EC000441

Описание класса ETIM 6.0: Кабельный ввод

Поставляемые цвета:

RAL 7001 серебристо-серый

RAL 7035 светло-серый

RAL 9005 чёрный

Последнее обновление (29.04.2024)

©2024 Lapp Group - all rights reserved.

Экономическое управление по продукту <http://lapprussia.lappgroup.com>

Вы можете посмотреть техническую информацию по продукту в с тех.паспорте

PN 0456 / 02_03.16

SKINTOP® ST-M L-BOXX

Комментарий

Фотографии и иллюстрации представлены не в точном масштабе и не являются точными до подробностей иллюстрациями соответствующих изделий.

Указаны «чистые» цены без учета НДС и надбавок. Продажа юридическим лицам.

SKINTOP® ST-M L-BOXX

Артикул	Обозначение/Размер	Ø F mm	Количество
53110050	SKINTOP® ST-M L-BOXX (SGY)	-	1
53110051	SKINTOP® ST-M L-BOXX (LGY)	-	1
53110052	SKINTOP® ST-M L-BOXX (BK)	-	1