

SKINDICHT® E-M HYGIENIC

Преимущества

Hygienic design with smooth surfaces and contours without corners and edges prevents residues such as liquids and micro-organisms from accumulating and posing a risk of contamination for food processing machinery. This facilitates simple, frequent and safe product cleaning.

Corrects the size difference between the connection thread of a cable gland and the threaded hole in an enclosure.

Provides flexibility in the selection of a cable gland, as the selection is independent to the threaded hole of the enclosure.

Multiple food and beverage certifications for Europe and North America.

Tested resistance to ECOLAB® disinfectants and cleaning agents.

Области применения

For use with metric SKINTOP® HYGIENIC/SKINTOP® INOX-M cable glands, whose Connection thread is larger than the existing threaded hole.

Especially for hygiene-critical areas of the food industry, where the product needs to be installed in the product zone or in the direct food production environment.

Also suitable for use in hygiene-critical areas of the pharmaceutical and chemical industry.

Withstands high chemical and mechanical stress.

Стандарты / Сертификаты соответствия

FKM-sealing compliant acc. FDA 21 CFR 177.2600

Конструкция

Метрическая соединительная резьба в соответствии с EN 50262

Техническая информация на основе DIN IEC 62444

Техническая информация

Классификация ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: кабельный ввод с резьбой

Классификация ETIM 6:

Обозначение класса ETIM 6.0: EC000441

Описание класса ETIM 6.0: Кабельный ввод

Поставляемые цвета:

Sealing: RAL 5015 (sky blue)

Материал:

Корпус: Нерж. сталь — V4A (1.4404 / 316L) Уплотнение: FKM

Температурный диапазон:

-20°C up to 220°C

Комментарий

Фотографии и иллюстрации представлены не в точном масштабе и не являются точными до подробностей иллюстрациями соответствующих изделий.

Указаны «чистые» цены без учета НДС и надбавок. Продажа юридическим лицам.

**SKINDICHT® E-M HYGIENIC**

Артикул	Резьба наружная M1	Резьба внутренняя M2	Общая высота, мм	SW и размер ключа, мм	Длина наружной резьбы, мм	Наружный Ø в мм	Штук/ед. упаковки
52103591	12 x 1,5	16 x 1,5	20,5	20	6,5	22.8	5
52103592	16 x 1,5	20 x 1,5	23	24	7	23.0	5
52103593	20 x 1,5	25 x 1,5	24	29	8	31.8	5
52103594	25 x 1,5	32 x 1,5	26,5	36	8	39.6	5

Последнее обновление (21.08.2024)

©2024 Larr Group - all rights reserved.

Экономическое управление по продукту <http://larrussia.larrgroup.com>

Вы можете посмотреть техническую информацию по продукту в с тех.паспорте
PN 0456 / 02_03_16