

## SKINDICHT® SM

SKINDICHT® SM, контргайки для тонкостенных корпусов со сквозными отверстиями, для использования в качестве ответного соединительного элемента для сальника



### Преимущества

Available in sizes PG7 to PG48.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

### Области применения

For locking a SKINTOP® /SKINDICHT® cable gland on the inside of the application (e.g. housing).

For thin-walled housings without a thread, which only allow one through-hole.

Withstands high mechanical loads.

### Конструкция

Соединительная резьба PG

### Техническая информация

Классификация ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Контргайка для кабельного ввода с резьбовым соединением

Классификация ETIM 6:

Обозначение класса ETIM 6.0: EC000940

Описание класса ETIM 6.0: Контргайка для кабельного ввода

Материал:

Латунь, покрытая никелем

Температурный диапазон:

от -60 до +200 °C

### Комментарий

Фотографии и иллюстрации представлены не в точном масштабе и не являются точными до подробностей иллюстрациями соответствующих изделий.

Указаны «чистые» цены без учета НДС и надбавок. Продажа юридическим лицам.



## SKINDICHT® SM

Артикул	Обозначение/Размер	Высота (мм)	SW и размер ключа, мм	Размер дальнего угла	Штук/ед. упаковки
SKINDICHT® SM					
52003490	PG 7	2.8	15	16,6	100
52003500	PG 9	2.8	18	20	100
52003510	PG 11	3.0	21	23,5	100
52003520	PG 13,5	3.0	23	25,5	100
52003530	PG 16	3.0	26	29	100
52003540	PG 21	3.5	32	35,5	50
52003550	PG 29	4.0	41	45	50
52003560	PG 36	5.0	51	56	25
52003570	PG 42	5.0	60	65	25
52003580	PG 48	5.5	64	69	25
52003490LF	PG 7	2.8	15	16,6	100
52003500LF	PG 9	2.8	18	20	100
52003510LF	PG 11	3.0	21	23,5	100
52003520LF	PG 13,5	3.0	23	25,5	100
52003530LF	PG 16	3.0	26	29	100
52003540LF	PG 21	3.5	32	35,5	50
52003550LF	PG 29	4.0	41	45	50
52003560LF	PG 36	5.0	51	56	25
52003570LF	PG 42	5.0	60	65	25
52003580LF	PG 48	5.5	64	69	25

Последнее обновление (08.05.2024)

©2024 Larr Group - all rights reserved.

Экономическое управление по продукту <http://larrussia.larrgroup.com>

Вы можете посмотреть техническую информацию по продукту в с тех.паспорте  
PN 0456 / 02\_03\_16