

## EPIC® H-A 3 TG

Инновационные корпуса из металла и полимеров

Locks reliably, does not burn, and protects the internal insert from dust and moisture: these are just three of the essential features of our newly revamped rectangular connector housing. The lightweight polyamide hood is also halogen-free, UV-resistant and has an M20 thread for connecting a cable or conduit gland.

### Информация

The hood of the EPIC® H-A 3 series is now available with a new design, including a marking arrow and an M20 thread.



Машиностроение, промышленное оборудование



Механическая стойкость



Износостойкие



Водонепроницаемые

### Преимущества

The EPIC® H-A 3 series comprises the smallest housings in the heavy-duty industrial connector range and ensures secure connections in the smallest of spaces.

The hood housing is mateable with many commercially available housings (panel-mount base, surface-mount base or coupler hood housings).

With threaded hole for use with a corresponding cable gland.

Articles with a "V" in the article name already contain a SKINTOP® plastic cable gland for sealing and strain-relieving cable entry.

In comparison to housings where the cable gland is added separately, the overall size of this housing is more space-saving.

The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.

### Области применения

To protect the connector insert from environmental influences.

Последнее обновление (24.04.2024)

©2024 Lapp Group - all rights reserved.

Экономическое управление по продукту <http://lapprussia.lappgroup.com>

Вы можете посмотреть техническую информацию по продукту в с тех.паспорте

PN 0456 / 02\_03.16

## EPIC® H-A 3 TG

For use with many EPIC® rectangular connector inserts.  
For connecting devices and machines to the power supply.  
Suitable for outdoor use.

### Характеристики

Корпус  
Винты для продольной скобы  
Ввод кабеля прямо  
Типы с/ без резьбового соединения

### Техническая информация

|                         |                                                                                                                      |
|-------------------------|----------------------------------------------------------------------------------------------------------------------|
| Классификация ETIM 5:   | ETIM 5.0 Class-ID: EC000437<br>ETIM 5.0 Class-Description: Корпус для промышленных электрических соединителей        |
| Классификация ETIM 6:   | Идентификатор класса ETIM 6.0: EC000437<br>Описание класса ETIM 6.0: Корпус для промышленного штекерного соединителя |
| Материал:               | Термопласт серый, черный Скоба: оцинкованная сталь                                                                   |
| Класс защиты:           | IP 65 (в закрытом виде)<br>NEMA 250, UL50E: 12, 4 (заблокированный)                                                  |
| VDE-испытания:          | Экспертиза с проверкой производства: VDE-регистрац.<br>№:B437<br>UL-испытан:<br>Регистрационный номер UL:E75770      |
| Температурный диапазон: | от -40 °C до +100 °C, кратковременно до +125 °C                                                                      |

### Комментарий

Фотографии и иллюстрации представлены не в точном масштабе и не являются точными до подробностей иллюстрациями соответствующих изделий.

Указаны «чистые» цены без учета НДС и надбавок. Продажа юридическим лицам.

## EPIC® H-A 3 TG

| Артикул  | Обозначение       | M  | PG | Материал   | Цвет   | Кабельный ввод | Диапазон зажима кабелей | Штук/ед. упаковки |
|----------|-------------------|----|----|------------|--------|----------------|-------------------------|-------------------|
| 10426000 | H-A 3 TG PG11 gr  | -  | 11 | Термопласт | серый  | -              | -                       | 10                |
| 10425500 | H-A 3 TG PG11 bk  | -  | 11 | Термопласт | чёрный | -              | -                       | 10                |
| 10426400 | H-A 3 TGV PG11 gr | -  | 11 | Термопласт | серый  | да             | 6.5 - 12                | 10                |
| 10426700 | H-A 3 TGV PG11 bk | -  | 11 | Термопласт | чёрный | да             | 6.5 - 12                | 10                |
| 19426000 | H-A 3 TG M20 gr   | 20 | -  | Термопласт | серый  | -              | -                       | 10                |
| 19425500 | H-A 3 TG M20 bk   | 20 | -  | Термопласт | чёрный | -              | -                       | 10                |
| 19426400 | H-A 3 TGV M20 gr  | 20 | -  | Термопласт | серый  | да             | 3.0 - 13.5              | 10                |
| 19426700 | H-A 3 TGV M20 bk  | 20 | -  | Термопласт | чёрный | да             | 3.0 - 13.5              | 10                |

## EPIC® H-A 3 TG

