

EPIC® H-A 3 TGB

Инновационные корпуса из металла и полимеров

Locks reliably, does not burn, and protects the internal insert from dust and moisture: these are just three of the essential features of our newly revamped rectangular connector housing. The lightweight polyamide cable coupler hood is also halogen-free, UV-resistant and has an M20 thread for connecting a cable gland or conduit gland.

Информация

The cable coupler hood of the EPIC® H-A 3 series is now available with a new design, including a marking arrow and an M20 thread.



Машиностроение, промышленное оборудование



Механическая стойкость



Износостойкие



Водонепроницаемые

Преимущества

The EPIC® H-A 3 series comprises the smallest housings in the heavy-duty industrial connector range and ensures secure connections in the smallest of spaces.

The coupling housing is mateable with many commercially available hood housings.

The "flying" connection between the cable coupler and the hood is not fixed, and acts as an extension of the cable.

The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.

The locking takes place using a plastic single lever.

Области применения

To protect the connector insert from environmental influences.

For use with many EPIC® rectangular connector inserts.

For connecting devices and machines to the power supply.

Suitable for outdoor use.

Характеристики

Корпус подвижный

1 скоба

Ввод кабеля прямо

Типы с/ без резьбового соединения

Техническая информация

Классификация ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Корпус для промышленных электрических соединителей

Последнее обновление (11.05.2024)

©2024 Lapp Group - all rights reserved.

Экономическое управление по продукту <http://lapprussia.lappgroup.com>

Вы можете посмотреть техническую информацию по продукту в с тех.паспорте

PN 0456 / 02_03.16

EPIC® H-A 3 TGB

Классификация ETIM 6:	Идентификатор класса ETIM 6.0: EC000437 Описание класса ETIM 6.0: Корпус для промышленного штекерного соединителя
Материал:	Термопласт серый, черный Скоба: оцинкованная сталь
Класс защиты:	IP 65 (в закрытом виде) NEMA 250, UL50E: 12, 4 (заблокированный)
VDE-испытания:	Экспертиза с проверкой производства: VDE-регистрац. №:B437 UL-испытан: Регистрационный номер UL:E75770
Температурный диапазон:	от -40 °C до +100 °C, кратковременно до +125 °C

Комментарий

Фотографии и иллюстрации представлены не в точном масштабе и не являются точными до подробностей иллюстрациями соответствующих изделий.

Указаны «чистые» цены без учета НДС и надбавок. Продажа юридическим лицам.

EPIC® H-A 3 TGB

Артикул	Обозначение	M	PG	Материал	Цвет	Кабельный ввод	Диапазон зажима кабелей	Штук/ед. упаковки
10429000	H-A 3 TGB PG11 gr	-	11	Термопласт	серый	-	-	10
10429200	H-A 3 TGB PG11 bk	-	11	Термопласт	чёрный	-	-	10
10429100	H-A 3 TGVB PG11 gr	-	11	Термопласт	серый	да	6.5 - 12	10
10620300	H-A 3 TGVB PG11 bk	-	11	Термопласт	чёрный	да	6.5 - 12	10
19429000	H-A 3 TGB M20 gr	20	-	Термопласт	серый	-	-	10
19429200	H-A 3 TGB M20 bk	20	-	Термопласт	чёрный	-	-	10
19429100	H-A 3 TGVB M20 gr	20	-	Термопласт	серый	да	3.0 - 13.5	10
19620300	H-A 3 TGVB M20 bk	20	-	Термопласт	чёрный	да	3.0 - 13.5	10